

Friction ring

REIB-RING SGM 50 HT2-65

Part no.:10.01.17.00412

<https://www.schmalz.com/10.01.17.00412>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > REIB-RING SGM 50 HT2-65

Friction ring




Construction use: Magnetic gripper

Size: 50

External diameter D: 50 mm

Internal diameter d: 41.5 mm

Design Data



Attribute	Value
D	50 mm
L	10.70 mm

Technical Data

Attribute	Value
Size	50
Suction cup material	High temperature material HT2
Operating temperature (max.)	200 °C
Material hardness [Shore A]	65 Shore A
Weight	4.70 g

Operating temperature max. short-term up to +250 °C

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx