

Inline ejector

SLP 05 S01

Part no...:10.02.01.00561

<https://www.schmalz.com/10.02.01.00561>


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Inline Ejectors > Inline Ejectors SLP > SLP 05 S01

Inline ejector for vacuum generation directly in the hose



Nozzle diameter:	0.5 mm
Degree of evacuation:	85 %
Connection:	Hose D4(1)-D4(2)
Suction rate (max.):	8 l/min
Air consumption suction:	13 l/min
Pressure optimal:	4.5 bar

Design Data



Attribute	Value
d	4 mm
D	10 mm
L	57 mm

Technical Data

Attribute	Value
Nozzle diameter	0.50 mm
Degree of evacuation	85 %
Suction rate (max.)	8 l/min
Suction rate (max.)	0.50 m³/h
Air consumption suction	13 l/min
Air consumption suction	0.80 m³/h
Sound level suction	52 dB(A)
Sound level free	60 dB(A)
Pressure optimal	4.50 bar

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Inline ejector

SLP 05 S01

Part no.:10.02.01.00561

<https://www.schmalz.com/10.02.01.00561>

Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	2 mm
Weight	5 g
Operating temperature	0 ... 60 °C
Pressure optimal	65.20 psi
Suction rate (max.)	0.28 cfm
Air consumption suction	0.46 cfm
Product family	SLP

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx