

Bellows suction cups (round)

FSG 3 NBR-55 M5-AG

Part no.:10.01.06.03717

<https://www.schmalz.com/10.01.06.03717>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 3 NBR-55 M5-AG

Bellows suction cup (round) for very uneven workpieces



Size: 3

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: M5-M

Number of folds: 2.5

Vacuum connection: M5-M

Design Data



Attribute	Value
d2	1.80 mm
dn	1 mm
Dmax(S)	4 mm
Ds	3 mm
G1	M5-M
H	10.20 mm
LG1	4.50 mm
SW1	7 mm
Z (Stroke)	1.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	3
Number of folds	2.50
Connection	M5-AG
Curve radius (min) (convex)	4 mm
Volume	0.02 cm ³

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 87624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSG 3 NBR-55 M5-AG

Part no.:10.01.06.03717

<https://www.schmalz.com/10.01.06.03717>

Suction force (-600mbar)	0.15 N
Pull-off force	0.40 N
Hose diameter (rec.) d	2 mm
Weight	0.70 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N055 M5-AG DN100

Part no.:10.01.01.13084

Thread G1: M5-M

Fitting length: 3.5 mm

Material: Aluminum



FG 3 NBR-55 N055

Part no.:10.01.06.03704

Size: 3

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr