

Flat suction cup (round)


SUF 80 HT1-60 G1/4-IG

Part no.:10.01.01.14084

<https://www.schmalz.com/10.01.01.14084>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 80 HT1-60 G1/4-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 80

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	87.10 mm
Ds	80 mm
dn	5.10 mm
G1	G1/4"-F
H	34.90 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	254 N
Pull-off force	254 N
Volume	25.10 cm ³
Curve radius (min) (convex)	100 mm
Hose diameter (rec.) d	6 mm
Size	80
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 80 HT1-60 G1/4-IG

Part no.:10.01.01.14084

<https://www.schmalz.com/10.01.01.14084>

Weight	72.80 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m
