

Bellows suction cups (round)

FSGPL 150 NBR-55 G1/2-IG

Part no.:10.01.06.00101

<https://www.schmalz.com/10.01.06.00101>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGPL (1.5 Folds) > FSGPL 150 NBR-55 G1/2-IG

Bellows suction cup (round) for large, heavy and uneven workpieces



Size: 150

Suction cup material: Nitrile rubber NBR


Material hardness [Shore A]: 55 Shore A

Nipple material: Steel

Vacuum connection: G1/2"-F

Number of folds: 1.5

Design Data



Attribute	Value
d2	93 mm
d3	69.40 mm
D1	155 mm
Dmax(S)	160 mm
Ds	143.50 mm
G1	G1/2"-F
H	51 mm
H4	8 mm
LG1	8 mm
Z (Stroke)	35.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	370 N
Pull-off force	500 N
Volume	449.34 cm ³
Curve radius (min) (convex)	250 mm
Hose diameter (rec.) d	12 mm
Size	150
Suction cup material	Nitrile rubber NBR

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr

Bellows suction cups (round)

FSGPL 150 NBR-55 G1/2-IG

Part no.:10.01.06.00101

<https://www.schmalz.com/10.01.06.00101>

Material hardness [Shore A]	55 Shore A
Weight	433 g
Number of folds	1.50
Product family	FSGPL

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Contact Schmalz

Schmalz Co. Ltd. | #503~507, 118 LS-ro 116Beon-gil, Dongan-gu, Anyang-si, Gyeonggi-do, 14118, South Korea | +82 31 89624031
schmalz@schmalz.co.kr