# Flat suction cup (round)

SUF 15 HT1-60 G1/8-AG

Part no..:10.01.01.14145

https://www.schmalz.com/10.01.01.14145




## Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 15
- Suction cup material: High temperature material HT1
- Material hardness [Shore A]: 60 Shore A
- Vacuum connection: G1/8"-M

## Design Data




| Attribute | Value |
|---|---|
| Dmax(S) | 16.80 mm |
| Ds | 15 mm |
| dn | 3.10 mm |
| G1 | G1/8"-M |
| H | 15 mm |
| LG1 | 7.50 mm |
| SW1 | 14 mm |
| Z (Stroke) | 1.50 mm |

## Technical Data

| Attribute | Value |
|---|---|
| Suction force (-600mbar) | 9 N |
| Pull-off force | 9 N |
| Volume | 0.22 cm³ |
| Curve radius (min) (convex) | 20 mm |
| Hose diameter (rec.) d | 4 mm |
| Size | 15 |
| Suction cup material | High temperature material HT1 |
| Material hardness [Shore A] | 60 Shore A |

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

# Flat suction cup (round)

SUF 15 HT1-60 G1/8-AG

Part no..:10.01.01.14145

https://www.schmalz.com/10.01.01.14145

| | |
|---|---|
| Weight | 4.70 g |
| Product family | SUF |
| Number of folds | 0 |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

## Spare parts



**SC 030 G1/8-AG**

Part no..:10.01.06.04288

| |
|---|
| Connection geometry: 030 |
| Vacuum connection: G1/8"-M |
| Fitting length: 6 mm |
| Nominal diameter dn: 3.1 mm |



**SUF 15 HT1-60 SC030**

Part no..:10.01.01.13989

| |
|---|
| Size: 15 |
| Suction cup material: High temperature material HT1 |
| Material hardness [Shore A]: 60 Shore A |