

Flat suction cup (round)


SUF 5 HT1-60 SC020

Part no.:10.01.01.13984

<https://www.schmalz.com/10.01.01.13984>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 5 HT1-60 SC020

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 5

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Design Data



Attribute	Value
d1	4.70 mm
d	3.10 mm
Dk	6.70 mm
Dmax(S)	5.70 mm
Ds	5 mm
H	5.50 mm
H2	2.30 mm
H3	3 mm
Z (Stroke)	0.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	0.90 N
Pull-off force	0.90 N
Volume	0.01 cm ³
Curve radius (min) (convex)	8 mm
Size	5
Nipple family	SC020
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Weight	0.10 g

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Flat suction cup (round)

SUF 5 HT1-60 SC020

Part no.:10.01.01.13984

<https://www.schmalz.com/10.01.01.13984>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 020 M5-AG

Part no.:10.01.06.04273

Connection geometry: 020

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm



SC 020 M5-IG

Part no.:10.01.06.04306

Connection geometry: 020

Vacuum connection: M5-F

Fitting length: 8.7 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx