

Flat suction cup (round)

PFG 95 NBR-55 N009 M10x1.25-IG

Part no.:10.01.01.00020

<https://www.schmalz.com/10.01.01.00020>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 95 NBR-55 N009 M10x1.25-IG

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 95

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
Dk	68.20 mm
Dmax(S)	102 mm
Ds	95 mm
H	21.50 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	350 N
Volume	37.09 cm ³
Curve radius (min) (convex)	200 mm
Size	95
Nipple family	N 009
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | +52 442 209 5211
schmalz@schmalz.com.mx

Flat suction cup (round)

PFG 95 NBR-55 N009 M10x1.25-IG

Part no.:10.01.01.00020

<https://www.schmalz.com/10.01.01.00020>

Weight	92.80 g
Product family	PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories




SA-NIP N009 G1/4-AG

Part no.:10.01.01.10097

Thread G1: G1/4"-M

Length L1: 25 mm

Material: Aluminum



SA-NIP N009 G1/4-IG

Part no.:10.01.01.10096

Thread G1: G1/4"-F

Length L1: 33 mm

Material: Aluminum

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Flat suction cup (round)

PFG 95 NBR-55 N009 M10x1.25-IG

Part no...:10.01.01.00020

<https://www.schmalz.com/10.01.01.00020>



SU 100

Part no...:10.01.01.12840

Size: 100

Clamping range: 100.0 ... 115.0 mm

Temperature resistance: 80 °C

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | +52 442 209 52 26
schmalz@schmalz.com.mx