

Bell suction cup (round)

SAX 40 ED-85 G1/4-IG

Part no.:10.01.19.00180

<https://www.schmalz.com/10.01.19.00180>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 40 ED-85 G1/4-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 40


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: G1/4"-F

Number of folds: 0

Design Data



Attribute	Value
dn	6.75 mm
Dmax(S)	45.40 mm
Ds	41.30 mm
G1	G1/4"-F
H	36.10 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	7.10 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	69 N
Lateral force	49 N
Lateral force (oily surface)	71 N
Volume	8.50 cm ³
Curve radius (min) (convex)	25 mm
Size	40
Connection	G1/4"-F
Number of folds	0

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | + 52 442 209 52 26
schmalz@schmalz.com.mx



Bell suction cup (round)

SAX 40 ED-85 G1/4-IG

Part no.:10.01.19.00180

<https://www.schmalz.com/10.01.19.00180>

Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	38.30 g
Product family	SAX

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx