Flat suction cup (round)

SAF 50 NBR-60 RA

Part no..:10.01.01.10796

https://www.schmalz.com/10.01.01.10796


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAF > SAF 50 NBR-60 RA

Flat suction cup (round) for very dynamic handling of smooth and oily workpieces



- Size: 50
- Suction cup material: Nitrile rubber NBR
- Material hardness [Shore A]: 60 Shore A
- Nipple material: Aluminum
- Connection: RA

Design Data



Attribute	Value
dn	6 mm
Dmax(S)	56 mm
Ds	50 mm
H	27.50 mm
L4	31.80 mm
SW1	22 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	100 N
Lateral force	80 N
Lateral force (oily surface)	76 N
Volume	9.48 cm^3
Curve radius (min) (convex)	65 mm
Hose diameter (rec.) d	4 mm
Size	50

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SAF 50 NBR-60 RA

Part no..:10.01.01.10796

https://www.schmalz.com/10.01.01.10796

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	39.90 g
Number of folds	0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 50

Part no..:10.01.01.12837

Size: 50
Clamping range: 45.0 ... 60.0 mm
Temperature resistance: 80 °C

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl