

Flat suction cup (round)

SUF 100 SI-55 G1/4-IG

Part no.:10.01.01.14076

<https://www.schmalz.com/10.01.01.14076>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 100 SI-55 G1/4-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 100


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Vacuum connection: G1/4"-F

Design Data



Attribute	Value
Dmax(S)	108 mm
Ds	100 mm
dn	5.10 mm
G1	G1/4"-F
H	35.90 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	7.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	402 N
Pull-off force	402 N
Volume	46.40 cm ³
Curve radius (min) (convex)	200 mm
Hose diameter (rec.) d	6 mm
Size	100
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 100 SI-55 G1/4-IG

Part no.:10.01.01.14076

<https://www.schmalz.com/10.01.01.14076>

Weight	113.80 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m
