Flat suction cup (round)


SUF 25 SI-55 G1/8-IG

Part no..:10.01.01.14136

https://www.schmalz.com/10.01.01.14136


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 25 SI-55 G1/8-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



- Size: 25
- Suction cup material: Silicone SI
- Material hardness [Shore A]: 55 Shore A
- Material characteristics: FDA-compatible
- Vacuum connection: G1/8"-F

Design Data



Attribute	Value
Dmax(S)	28.20 mm
Ds	25 mm
dn	4.10 mm
G1	G1/8"-F
H	25.20 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	2.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	23 N
Pull-off force	23 N
Volume	0.90 cm³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	4 mm
Size	25
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 25 SI-55 G1/8-IG

Part no..:10.01.01.14136

https://www.schmalz.com/10.01.01.14136

Weight	10.50 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 040 G1/8-IG

Part no..:10.01.06.02482

Connection geometry: 040
Connection: G1/8"-F
Length L1: 20.7 mm
Fitting length: 14 mm
Nominal diameter dn: 4.1 mm



SUF 25 SI-55 SC040

Part no..:10.01.01.13970

Size: 25
Suction cup material: Silicone SI
Material characteristics: FDA-compatible
Material hardness [Shore A]: 55 Shore A