Vacuum pump

EVE-TR 60 AC3 IE3-TYP1 F

Part no..:10.03.01.00335

https://www.schmalz.com/10.03.01.00335


Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Dry-Running Vacuum Pumps EVE-TR > EVE-TR 60 AC3 IE3-TYP1 F

Oil-free pump with constant suction rate, robust, requires little maintenance



- Current type: three-phase current
- Sound level at 50 Hz: 71 dB(A)
- Voltage at 50Hz: D230V/Y400V ±10%
- Voltage at 60Hz: D265V/Y460V ±10%
- Suction rate (60 Hz): 66 m³/h
- Vacuum (50 Hz): -900 mbar
- Rated power 50 Hz: 2.2 kW
- Rated power 60 Hz: 2.6 kW
- Construction: IE3:EU/CN/IND
- with: Filter
- Permission: IE3
- Weight: 76 kg

Design Data



Attribute	Value
B	353 mm
B2	46 mm
d	12 mm
G2	G1-1/4"-F
G3	G1"-F
G5	M8-F
H	328 mm
H1	415 mm
H2	75 mm
L	704 mm
L1	740 mm
L2	96 mm
X1	326 mm
Y1	190 mm
Y2	95 mm

Technical Data

Attribute	Value
Suction rate (60 Hz)	66 m³/h

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuum pump

EVE-TR 60 AC3 IE3-TYP1 F

Part no..:10.03.01.00335

https://www.schmalz.com/10.03.01.00335

Voltage at 50Hz	D230V/Y400V ±10%
Voltage at 60Hz	D265V/Y460V ±10%
Rated power 50 Hz	2.20 kW
Rated power 60 Hz	2.60 kW
Current type	AC3
Current type	three-phase current
Construction	IE3:EU/CN/IND
Sound level at 50 Hz	71 dB(A)
Weight	76 kg
Protection type IP	IP 55
Product family	EVE-TR

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

Spare parts



VST EVE-TR60/TR80

Part no..:22.09.01.00031

Construction use: Pump EVE
Size: TR60/TR80
contains: Brush slide
and: Filter

Contact Schmalz
Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl