

Flat suction cup (round)

SUF 10 SI-CO-55 M5-IG

Part no...:10.01.01.14174

<https://www.schmalz.com/10.01.01.14174>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 10 SI-CO-55 M5-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 10

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Vacuum connection: M5-F

Design Data



Attribute	Value
Dmax(S)	11.20 mm
Ds	10 mm
dn	3.10 mm
G1	M5-F
H	18.40 mm
LG1	5.50 mm
SW1	8 mm
Z (Stroke)	1 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	4 N
Pull-off force	4 N
Volume	0.07 cm ³
Curve radius (min) (convex)	12.50 mm
Hose diameter (rec.) d	2 mm
Size	10
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 10 SI-CO-55 M5-IG

Part no.:10.01.01.14174

<https://www.schmalz.com/10.01.01.14174>

Weight	1.80 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC 030 M5-IG

Part no.:10.01.06.03440

Connection geometry: 030

Connection: M5-F

Length L1: 15.8 mm

Fitting length: 10 mm

Nominal diameter dn: 3.1 mm



SUF 10 SI-CO-55 SC030

Part no.:10.01.01.14029

Size: 10

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A