

Vacuum cup filter

VFT G1/4-IG 100

Part no.: 10.07.01.00120

<https://www.schmalz.com/10.07.01.00120>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Cup Filters VFT > VFT G1/4-IG 100

Vacuum cup filter with transparent housing and replaceable filter



Connection: G1/4"-F


Shape: Short filter insert

Nominal flow rate: 140 l/min

Nominal flow rate: 8.4 m³/h

Filter pore size: 100 µm

Design Data



Attribute	Value
D	48 mm
G1	G1/4"-F
H	60 mm
H1	50 mm
L	76 mm

Technical Data

Attribute	Value
Connection	G1/4"-F
Nominal flow rate	140 l/min
Nominal flow rate	8.40 m³/h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Filter pore size	100 µm
Weight	47 g

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuum cup filter

VFT G1/4-IG 100

Part no.:10.07.01.00120

<https://www.schmalz.com/10.07.01.00120>

Product family

VFT

Spare parts



FILT-EINS 100 25x37 A2 VFT-1/8+1/4

Part no.:10.07.01.00132

Filter pore size: 100 µm

External diameter D: 25 mm

Length L: 37 mm

Filter material: Aust. Stainless steel

Construction use: Filters VFT

Size: 1/8+1/4



HTR-FIL 2S WI VFT1/8-1/2

Part no.:10.07.01.00228

Shape: angled



DR 37-33x3 NBR

Part no.:10.07.01.00154

External diameter D: 37 mm

Length L: 3 mm

Internal diameter d: 33 mm

Material: Nitrile rubber NBR

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl



Vacuum cup filter

VFT G1/4-IG 100

Part no...:10.07.01.00120

<https://www.schmalz.com/10.07.01.00120>

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl