

Tooling-System-Schmalz-Ejektor

SEAC 10 VE-SH

Part no.:10.02.02.03876

<https://www.schmalz.com/10.02.02.03876>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Decentralized Ejectors > Ejectors with Active Blow Off
SEAC > SEAC 10 VE-SH

Tooling-System-Schmalz-Ejektor




Nozzle diameter: 1 mm

Add. function: Vac switch elec / Protect Hood

Pressure range (operating pressure): 4.0 ... 6.0 bar

Design Data



Attribute	Value
B	31 mm
B1	34.60 mm
B3	15.50 mm
D	27 mm
d	7.50 mm
G1	G1/8"-F
G4	G1/8"-F
H	21.50 mm
H1	27.50 mm
H2	42.50 mm
L	46 mm
L1	77 mm
L3	6 mm
X1	28 mm

Technical Data

Attribute	Value
Nozzle diameter	1 mm
Degree of evacuation	85 %
Suction rate (max.)	35 l/min
Suction rate (max.)	2.10 m³/h

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Tooling-System-Schmalz-Ejector

SEAC 10 VE-SH

Part no.:10.02.02.03876

<https://www.schmalz.com/10.02.02.03876>

Air consumption suction	52 l/min
Air consumption suction	3.12 m³/h
Max. air consumption blow off	60 l/min
Air consumption blow off	3.60 m³/h
Pressure range (operating pressure)	4.0 ... 6.0 bar
Weight	157 g
Pressure range (operating pressure)	58.0 ... 87.0
Suction rate (max.)	1.24 cfm
Air consumption suction	1.84 cfm
Air consumption blow off	2.12 cfm
Operating temperature	0 ... 60 °C
Max. vacuum	25.10 inHg
Product family	SEAC

Note: Air consumption: At optimal operating pressure (4,5 bar)