

Flat suction cup (oval)

SAOF 80x40 NBR-60 RA

Part no.:10.01.05.00299

<https://www.schmalz.com/10.01.05.00299>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 80x40 NBR-60 RA

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 80x40

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: RA

Design Data



Attribute	Value
Bmax(S)	43 mm
Bs	38.60 mm
dn	4 mm
H	23 mm
L4	32 mm
Lmax(S)	85 mm
Ls	80.60 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	140 N
Lateral force	110 N
Lateral force (oily surface)	100 N
Volume	11.70 cm ³
Curve radius (min) (convex)	50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (oval)

SAOF 80x40 NBR-60 RA

Part no...:10.01.05.00299

<https://www.schmalz.com/10.01.05.00299>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	44 g
Product family	SAOF
Dimensions (LxB)	80x40

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m