

Feed ejector

SEC-750

Part no.:10.02.01.00081

<https://www.schmalz.com/10.02.01.00081>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-750


Powerful ejector for very porous parts



Nozzle size: 75 mm

Suction rate (max.): 518.4 m³/h

Design Data



Attribute	Value
D	140 mm
D1	125 mm
D2	100 mm
G2	G1/2"-F
G3	M6-F
L	65 mm
L1	180 mm
LG3	6 mm
X1	126 mm

Technical Data

Attribute	Value
Max. vacuum	-5 mbar
Suction rate (max.)	8640 l/min
Suction rate (max.)	518.40 m³/h
Air consumption suction	770 l/min
Air consumption suction	46.20 m³/h
Pressure range (operating pressure)	2.0 ... 6.0 bar
Operating temperature	-20 ... 80 °C
Weight	2.35 kg
Max. vacuum	-0.15 inHg

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Feed ejector

SEC-750

Part no...:10.02.01.00081

<https://www.schmalz.com/10.02.01.00081>

Suction rate (max.)	305.11 cfm
Air consumption suction	27.19 cfm
Pressure range (operating pressure)	29.0 ... 87.0
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)
