

Vacuum pump

EVE-OG 10 AC3 F

Part no.:10.03.02.00082

<https://www.schmalz.com/10.03.02.00082>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 10 AC3 F

Oil-lubricated pump for maximum vacuum levels, requires little maintenance



Suction rate (60 Hz): 12 m³/h

Current type: three-phase current

Sound level at 50 Hz: 49 dB(A)

with: Filter

Suction rate (50 Hz): 10 m³/h


Rated power 50 Hz: 0.37 kW

Voltage at 50Hz: 230/400V AC

Voltage at 60Hz: 230/400V - AC

Weight: 19 kg

Design Data



Attribute	Value
B	212 mm
B2	26 mm
G2	G3/4"-F
G3	G3/4"-F
G5	M8-F
H	211 mm
H1	320 mm
H2	70 mm
L	422 mm
L2	63 mm
X1	176 mm
Y1	111 mm

Technical Data

Attribute	Value
Max. vacuum	-980 mbar
Max. vacuum	-28.94 inHg
Suction rate (50 Hz)	10 m ³ /h
Voltage at 50Hz	230/400V AC
Rated power 50 Hz	0.37 kW
Sound level at 50 Hz	49 dB(A)

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Vacuum pump

EVE-OG 10 AC3 F

Part no...:10.03.02.00082

<https://www.schmalz.com/10.03.02.00082>

Weight	19 kg
Protection type IP	IP 54
Current type	AC3
Product family	EVE-OG

Accessories



DRM 40 P1 H

Part no...:10.07.02.00050

External diameter D: 40 mm

Measuring range: 0,0 ... 1,0 bar

Construction shape manometers: Connection at rear

Thread G1: G3/4"-M



OEL EVE-OG 1L ANDEROL 555

Part no...:27.02.01.00055

Construction use: Pump EVE-OG

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Vacuum pump

EVE-OG 10 AC3 F

Part no...:10.03.02.00082

<https://www.schmalz.com/10.03.02.00082>



ZUB EVE-OG Ölabblass-Kit

Part no...:22.09.03.00038

Construction use: Pump EVE-OG