

Bell suction cup (round)

SAX 50 ED-85 G1/4-IG

Part no.:10.01.19.00181

<https://www.schmalz.com/10.01.19.00181>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 50 ED-85 G1/4-IG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 50


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: G1/4"-F

Number of folds: 0

Design Data



Attribute	Value
dn	6.75 mm
Dmax(S)	58.40 mm
Ds	51.50 mm
G1	G1/4"-F
H	36.40 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	8.40 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	109 N
Lateral force	74 N
Lateral force (oily surface)	110 N
Volume	15.20 cm ³
Curve radius (min) (convex)	25 mm
Size	50
Connection	G1/4"-F
Number of folds	0

Contact Schmalz

Schmalz d.o.o. | Velika Ligojna 4, Vrhnika, Slovenia | +386 70 613 796 | info@schmalz.si

Bell suction cup (round)

SAX 50 ED-85 G1/4-IG

Part no.:10.01.19.00181

<https://www.schmalz.com/10.01.19.00181>

Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	39.50 g
Product family	SAX