

Vacuum cup filter

VFT G1/4-IG 80

Part no...:10.07.01.00119

<https://www.schmalz.com/10.07.01.00119>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Cup Filters VFT > VFT G1/4-IG 80

Vacuum cup filter with transparent housing and replaceable filter



Connection: G1/4"-F


Shape: Short filter insert

Nominal flow rate: 110 l/min

Nominal flow rate: 6.6 m³/h

Filter pore size: 80 µm

Design Data



Attribute	Value
D	48 mm
G1	G1/4"-F
H	60 mm
H1	50 mm
L	76 mm

Technical Data

Attribute	Value
Connection	G1/4"-F
Nominal flow rate	110 l/min
Nominal flow rate	6.60 m³/h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Filter pore size	80 µm
Weight	47 g

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0123 | schmalz@schmalz.com.tr

Vacuum cup filter

VFT G1/4-IG 80

Part no...:10.07.01.00119

<https://www.schmalz.com/10.07.01.00119>

Product family

VFT

Spare parts



FILT-EINS 80 25x37 PE VFT-1/8-1/4

Part no...:10.07.01.00141

Filter pore size: 80 µm

External diameter D: 25 mm

Length L: 37 mm

Filter material: Polyethylene

Construction use: Filters VFT

Size: 1/8-1/4



HTR-FIL 2S WI VFT1/8-1/2

Part no...:10.07.01.00228

Shape: angled



DR 37-33x3 NBR

Part no...:10.07.01.00154

External diameter D: 37 mm

Length L: 3 mm

Internal diameter d: 33 mm

Material: Nitrile rubber NBR

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0113 | schmalz@schmalz.com.tr



Vacuum cup filter

VFT G1/4-IG 80

Part no...:10.07.01.00119

<https://www.schmalz.com/10.07.01.00119>

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 310 0113 | schmalz@schmalz.com.tr