

Suction plate (round)

SPU 125 SI-60 G1/4-IG

Part no.:10.01.01.01103

<https://www.schmalz.com/10.01.01.01103>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Suction Plates SPU > SPU 125 SI-60 G1/4-IG

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 125

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Connection: G1/4"-F

Design Data



Attribute	Value
d	22 mm
d2	83 mm
d3	61 mm
Dmax(S)	132 mm
Ds	125 mm
G1	G1/4"-F
G2	G1/4"-F
H	25 mm
H1	26 mm
L2	22 mm
LG1	13 mm
LG2	14 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	660 N
Suction force d2	365 N
Volume	75.60 cm ³

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Suction plate (round)

SPU 125 SI-60 G1/4-IG

Part no.:10.01.01.01103

<https://www.schmalz.com/10.01.01.01103>

Curve radius (min) (convex)	220 mm
Hose diameter (rec.) d	9 mm
Size	125
Suction cup material	Silicone SI
Material hardness [Shore A]	60 Shore A
Weight	200 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 120

Part no.:10.01.01.12437

Size: 120

Clamping range: 115.0 ... 130.0 mm

Temperature resistance: 80 °C

Spare parts



DR-SPU 125 SI-60

Part no.:10.01.01.01100

Size: 125

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Suction plate (round)

SPU 125 SI-60 G1/4-IG

Part no...:10.01.01.01103

<https://www.schmalz.com/10.01.01.01103>
