

## Vacuum filter (inline)

VFI 4/2 50

Part no.:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

Homepage > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Inline Filters VFI > VFI 4/2 50


### Vacuum filter with replaceable filter cartridge



Connection: Hose 4/2

Filter pore size: 50 µm

### Design Data



Attribute	Value
d	4 mm
D	17 mm
L	55 mm

### Technical Data

Attribute	Value
Connection	Hose 4/2
Filter pore size	50 µm
Nominal flow rate	32 l/min

## Vacuum filter (inline)

VFI 4/2 50

Part no.:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

Attribute	Value
Nominal flow rate	1.92 m <sup>3</sup> /h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Weight	6.3 g

### Spare Parts



#### **FILT-EINS 50 10x21 VFI**

Part no.10.07.01.00244

Filter insert (round)


Filter pore size: 50 µm

External diameter D: 10 mm

Length L: 21 mm

Packaging unit: 5 pieces  
for: Vacuum filter (inline)

### Accessories



#### **FILT-EINS 50 10x21 VFI**

Part no.10.07.01.00244

Filter insert (round)

Filter pore size: 50 µm

External diameter D: 10 mm

Length L: 21 mm

Packaging unit: 5 pieces  
for: Vacuum filter (inline)