

Vacuum hose (meter)

VSL 61-50 PVC-DS GR

Part no.:10.07.09.00033

<https://www.schmalz.com/10.07.09.00033>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 61-50 PVC-DS GR

Hose for vacuum and compressed-air systems



External diameter D: 61 mm

Internal diameter d: 50 mm

Length max.: 10 m

Material hose: PVC with wire spiral

Bending radius min.: 90 mm

Pressure range (operating pressure): -0.78 ... 1.50 bar

Operating temperature: -20 ... 70 °C

Design Data



Attribute	Value
d	50 mm
D	61 mm

Technical Data

Attribute	Value
Hose type	61-50
Pressure range (operating pressure)	-0.78 ... 1.50 bar
Operating temperature	-20 ... 70 °C
Bending radius min.	90 mm
Length max.	10 m
Weight/Meter	541 g/m
Weight/Meter	0.54 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Vacuum hose (meter)

VSL 61-50 PVC-DS GR

Part no...:10.07.09.00033

<https://www.schmalz.com/10.07.09.00033>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 60-68 ST-VZ

Part no...:10.07.10.00017

Clamping range: 60.0 ... 68.0 mm

Material: Steel

Surface: galvanised

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr