

Vacuum regulator

VR G3/8-IG HW

Part no...:10.05.05.00026

<https://www.schmalz.com/10.05.05.00026>

Home > Vacuum Technology for Automation > Vacuum Components > Switches and System Monitoring > Measuring and Control Devices > Vacuum Regulators VR > VR G3/8-IG HW

Vacuum regulator to compensate for vacuum variations




Thread G1: G3/8"-F

Vacuum range: -990 ... -14 mbar

Additional function: Mounting bracket

Design Data



Attribute	Value
B	76.40 mm
B1	87.20 mm
B2	49 mm
G1	G3/8"-F
G2	G1/4"-F
H	176.80 mm
H2	82.30 mm
H3	9 mm
L	76 mm
X1	45 mm

Technical Data

Attribute	Value
Vacuum range	-990 ... -14 mbar
Repeatability	5 mbar
Flow rate max. vacuum	195 l/min
Flow rate max.	11.70 m³/h
Operating temperature	5 ... 60 °C
Weight	0.65 kg
Product family	VR

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr

Vacuum regulator

VR G3/8-IG HW

Part no...:10.05.05.00026

<https://www.schmalz.com/10.05.05.00026>

Accessories



RED-MUF-S G3/8-IG G1/4-IG MS

Part no...:10.08.04.00017

Thread G1: G3/8"-F

Thread G2: G1/4"-F

Material: Brass

Length L: 26 mm



RED-NIP G3/8-AG R3/8-AG MS

Part no...:10.08.05.00091

Thread G1: G3/8"-M

Thread G2: R3/8"-M

Material: Brass

Length L: 5 mm

Nominal diameter dn: 10 mm

Contact Schmalz

Schmalz Vakum San. ve Tic. Ltd. Sti. | Aydinli Mah. Patlayici Maddeler Yolu, Dumankaya Botanik A-89, 34953 Tuzla, Istanbul, Turkey | +90 216 340 0122 | schmalz@schmalz.com.tr