

Feed ejector

SEC-100

Part no.:10.02.01.00078

<https://www.schmalz.com/10.02.01.00078>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-100


Powerful ejector for very porous parts



Nozzle size: 10 mm

Suction rate (max.): 36.6 m³/h

Design Data



Attribute	Value
D	37 mm
D1	19 mm
D2	19 mm
G2	G1/8"-F
G3	M4-F
L	21 mm
L1	70 mm
LG3	8 mm
X1	29 mm

Technical Data

Attribute	Value
Max. vacuum	-170 mbar
Suction rate (max.)	610 l/min
Suction rate (max.)	36.60 m ³ /h
Air consumption suction	190 l/min
Air consumption suction	11.10 m ³ /h
Pressure range (operating pressure)	2.0 ... 6.0 bar
Operating temperature	-20 ... 80 °C
Weight	0.07 kg
Max. vacuum	-5.02 inHg

Contact Schmalz

Schmalz Inc. | 5850 Oak Forest Drive, Raleigh, NC 27616, United States | +1 (919) 713-0880 | schmalz.us@schmalz.com

Feed ejector

SEC-100

Part no...:10.02.01.00078

<https://www.schmalz.com/10.02.01.00078>

Suction rate (max.)	21.54 cfm
Air consumption suction	6.71 cfm
Pressure range (operating pressure)	29.0 ... 87.0
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)
