

Sealing profile (meter)

DI-PROF 10x20 MOS EPDM-20 HR

Part no.:10.07.04.00010

<https://www.schmalz.com/10.07.04.00010>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 10x20 MOS EPDM-20 HR

Sealing section for construction of specific gripper solutions



Width B: 10 mm

Height H: 20 mm


Material type: Foam rubber

Sealing material: EPDM

Material hardness [Shore A]: 20 Shore A

Form: half-round

Design Data



Attribute	Value
B	10 mm
H	20 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	EPDM
Recommended slot width x slot depth [mm]	11 x 10
Weight	89 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Sealing profile (meter)

DI-PROF 10x20 MOS EPDM-20 HR

Part no.:10.07.04.00010

<https://www.schmalz.com/10.07.04.00010>
