

Magnetic gripper

SGM-HT-HP 30 G1/8-IG

Part no.: 10.01.17.00397

<https://www.schmalz.com/10.01.17.00397>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Magnetic Grippers SGM-HP/-HT > SGM-HT-HP 30 G1/8-IG

Magnetic gripper for handling metal sheets with holes




Socket: G1/8"-F

Pressure range (operating pressure): 2.5 ... 6.0 bar

Holding force max. friction ring: 80 N

Holding force max. without friction ring: 120 N

Design Data



Attribute	Value
B	30.10 mm
B2	15 mm
D	26.90 mm
G1	G1/8"-F
G2	G1/8"-F
G4	M4-F
G5	M4-F
H	99.20 mm
H2	15.50 mm
L2	20.50 mm
LG1	6 mm
LG2	6 mm
LG4	5 mm
X1	74 mm
Y1	12 mm

Note: Contact surface of grippers without friction ring (stadium-shaped) corresponds to dimension D x B2; with friction ring (round) dimension D

Technical Data

Attribute	Value
Holding force max. without friction ring	120 N

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HT-HP 30 G1/8-IG

Part no...:10.01.17.00397

<https://www.schmalz.com/10.01.17.00397>

Holding force max. friction ring	80 N
Sheet thickness opt f. holding force max.	2 mm
Holding force 2mm-sheet without friction ring	120 N
Holding force 2mm-sheet friction ring	80 N
Remaining force	0.30 N
Pressure range (operating pressure)	2.5 ... 6.0 bar
Installation position	BEL
Control valve	Bistable
Working temperature max.	350 °C
Operating temperature	5 ... 150 °C
Weight	215 g
Product family	SGM-HP-HT

Note: The specified holding forces are static values under optimal conditions (primarily depending on material and surface characteristics). For system designs, a safety factor of $S = 3$ must be applied. Holding forces SGM-HT-HP at 20 °C; can be used for workpiece temperatures up to 350 °C (depending on process conditions), the influence of temperature can reduce holding forces by up to 30%

Accessories



HTS-A2 SGM-HP 30/40 OP

Part no...:10.01.17.00567

Connection 1: Bolt with slot Ø19mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40



HTS-A3 SGM-HP 30/40 OP

Part no...:10.01.17.00557

Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HT-HP 30 G1/8-IG

Part no...:10.01.17.00397

<https://www.schmalz.com/10.01.17.00397>




HTS-A5 SGM-HP 30/40 OP

Part no...:10.01.17.00563

Connection 1: Ball head 32 mm

Construction use: Magnetic gripper SGM-HP

Size: 30/40



HPS-SGM-HP 2M8 30/40 OP

Part no...:10.01.17.00651

Construction use: Magnetic gripper SGM-HP

Connection 1: 2x screws M8

Size: 30/40

Shape: One-piece



SCHUTZ SGM-30 ST

Part no...:10.01.17.00522

Construction use: Magnetic gripper

Size: 30

Material: Steel

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HT-HP 30 G1/8-IG

Part no.:10.01.17.00397

<https://www.schmalz.com/10.01.17.00397>



REIB-RING SGM 30 HT2-65

Part no.:10.01.17.00410

Construction use: Magnetic gripper

Size: 30

External diameter D: 29.5 mm

Internal diameter d: 20.5 mm



ADP-E-TRI 30/40 SET

Part no.:10.01.17.00421

Shape: Triangle

Workpiece diameter (min): 10 mm

Workpiece diameter (max): 20 mm



ADP-E-UNI 30/40 SET

Part no.:10.01.17.00423

Shape: rectangular

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Magnetic gripper

SGM-HT-HP 30 G1/8-IG

Part no...:10.01.17.00397

<https://www.schmalz.com/10.01.17.00397>



STV-GE G1/8-AG 6 HT

Part no...:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11.6 mm

Length L: 19 mm



STV-W G1/8-AG 6 HT

Part no...:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22.5 mm



VSL 6-4 PTFE MI-TR

Part no...:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de