

Vacuum hose (meter)

VSL 85-75 PVC-PS GR

Part no.:10.07.09.00048

<https://www.schmalz.com/10.07.09.00048>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 85-75 PVC-PS GR

Hose for vacuum and compressed-air systems



External diameter D: 85 mm

Internal diameter d: 75 mm

Length max.: 10 m


Material hose: PVC with PVC-spiral

Bending radius min.: 114 mm

Pressure range (operating pressure): -0.29 ... 1.00 bar

Operating temperature: -20 ... 70 °C

Design Data



Attribute	Value
d	75 mm
D	85 mm

Technical Data

Attribute	Value
Hose type	85-75
Pressure range (operating pressure)	-0.29 ... 1.00 bar
Operating temperature	-20 ... 70 °C
Bending radius min.	114 mm
Length max.	10 m
Weight/Meter	920 g/m
Weight/Meter	0.92 kg/m
Material hose	PVC with PVC-spiral

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 85-75 PVC-PS GR

Part no.:10.07.09.00048

<https://www.schmalz.com/10.07.09.00048>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 85-90 ST-VZ

Part no.:10.07.10.00102

Clamping range: 85.0 ... 90.0 mm

Material: Steel

Surface: galvanised