

Vacuum cup filter

VFT G3/8-IG 80

Part no.:10.07.01.00122

<https://www.schmalz.com/10.07.01.00122>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Vacuum Cup Filters VFT > VFT G3/8-IG 80

Vacuum cup filter with transparent housing and replaceable filter



Connection: G3/8"-F


Shape: Long filter insert

Nominal flow rate: 245 l/min

Nominal flow rate: 14.7 m³/h

Filter pore size: 80 µm

Design Data



Attribute	Value
D	48.50 mm
G1	G3/8"-F
H	101 mm
H1	88 mm
L	77.20 mm

Technical Data

Attribute	Value
Connection	G3/8"-F
Nominal flow rate	245 l/min
Nominal flow rate	14.70 m ³ /h
Max. vacuum	-990 mbar
Overpressure (max) at 25°C	7 bar
Overpressure (max) at 50°C	5 bar
Filter pore size	80 µm
Weight	79 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum cup filter

VFT G3/8-IG 80

Part no...:10.07.01.00122

<https://www.schmalz.com/10.07.01.00122>

Product family

VFT

Spare parts



FILT-EINS 80 25x71 PE VFT-3/8-1/2

Part no...:10.07.01.00143

Filter pore size: 80 µm

External diameter D: 25 mm

Length L: 71 mm

Filter material: Polyethylene

Construction use: Filters VFT

Size: 3/8-1/2



HTR-FIL 2S WI VFT1/8-1/2

Part no...:10.07.01.00228

Shape: angled



DR 37-33x3 NBR

Part no...:10.07.01.00154

External diameter D: 37 mm

Length L: 3 mm

Internal diameter d: 33 mm

Material: Nitrile rubber NBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum cup filter

VFT G3/8-IG 80

Part no...:10.07.01.00122

<https://www.schmalz.com/10.07.01.00122>
