

Feed ejector

SEC-200

Part no.:10.02.01.00079

<https://www.schmalz.com/10.02.01.00079>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Feed Ejectors > Feed Ejectors SEC > SEC-200


Powerful ejector for very porous parts



Nozzle size: 20 mm

Suction rate (max.): 82.5 m³/h

Design Data



Attribute	Value
D	50 mm
D1	38 mm
D2	32 mm
G2	G1/4"-F
G3	M4-F
L	30 mm
L1	90 mm
LG3	12 mm
X1	42 mm

Technical Data

Attribute	Value
Max. vacuum	-60 mbar
Suction rate (max.)	1370 l/min
Suction rate (max.)	82.50 m ³ /h
Air consumption suction	290 l/min
Air consumption suction	17.40 m ³ /h
Pressure range (operating pressure)	2.0 ... 6.0 bar
Operating temperature	-20 ... 80 °C
Weight	0.18 kg
Max. vacuum	-1.77 inHg

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Feed ejector

SEC-200

Part no...:10.02.01.00079

<https://www.schmalz.com/10.02.01.00079>

Suction rate (max.)	48.38 cfm
Air consumption suction	10.24 cfm
Pressure range (operating pressure)	29.0 ... 87.0
Product family	SEC

Note: Air consumption: At optimal operating pressure (4,5 bar)
