

Retrofitting kit


SET SBPL 75/100

Part no...:10.02.01.01685

<https://www.schmalz.com/10.02.01.01685>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > SET SBPL 75/100

Retrofit kit



Construction use: Basic ejector

Size: 75/100

Design Data



Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	590 g

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Retrofitting kit

SET SBPL 75/100

Part no...:10.02.01.01685

<https://www.schmalz.com/10.02.01.01685>



SEP HF 3 13 22

Part no...:10.02.01.01348

Shape: High Flow

Number of stages: 3

Nozzle size: 1.3 mm

Hole diameter: 22 mm

Degree of evacuation: 61 %

Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 297.6 l/min

Air consumption suction: 74 l/min



SEP HV 3 16 22

Part no...:10.02.01.01397

Shape: High Vacuum

Number of stages: 3

Nozzle size: 1.6 mm

Hole diameter: 22 mm

Degree of evacuation: 90 %

Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 308.8 l/min

Air consumption suction: 103 l/min



VRS-ST 15x101.7 SBPL

Part no...:10.02.01.01687

Construction use: Basic ejector

External diameter D: 15 mm

Length L: 101.7 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de