

Basic Ejector

SBP HV 2 04 7 KU

Part no.:10.02.01.01958

<https://www.schmalz.com/10.02.01.01958>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > Basic Ejectors SBP-HV/HF With Plastic Main Body > SBP HV 2 04 7 KU

Basic ejector for universal use



Shape: High Vacuum

Number of stages: 2

Nozzle diameter: 0.4 mm

Size: 7


Degree of evacuation: 79 %

Suction rate (max.): 13.2 l/min

Air consumption suction: 6.5 l/min

Material: Plastics

Design Data



Attribute	Value
B	19 mm
d2	4.20 mm
D	6 mm
G1	G1/8"-F
G2	G1/8"-F
G5	M4-F
H	25 mm
H2	5 mm
H3	12.50 mm
L	36.50 mm
L1	47.50 mm
L2	10 mm
L3	13.50 mm
SW2	4 mm
X1	12 mm
X2	19 mm
Y1	12 mm

Technical Data

Attribute

Value

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Basic Ejector

SBP HV 2 04 7 KU

Part no.:10.02.01.01958

<https://www.schmalz.com/10.02.01.01958>

Nozzle diameter	0.40 mm
Number of stages	2
Degree of evacuation	79 %
Suction rate (max.)	13.20 l/min
Air consumption suction	0.40 m³/h
Air consumption suction	6.50 l/min
Sound level free	65 dB(A)
Sound level suction	57 dB(A)
Pressure range (operating pressure)	2.0 ... 6.0 bar
Recomm. internal hose diameter compressed air	2 mm
Recomm. internal hose diameter vacuum	4 mm
Weight	21.50 g
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	29.0 ... 87.0
Suction rate (max.)	0.47 cfm
Air consumption suction	0.23 cfm
Product family	SBP-HV-HF-KU

Spare parts



SFE 7 POM

Part no.:10.02.01.01808

Hole diameter: 7 mm

Width B: 19 mm

Height H: 25 mm

Length L: 36.5 mm

Thread G1: M8x0.5-F

Thread G2: G1/8"-F

Compressed-air connection: M8x0.5-F

Suction cup connection: G1/8"-F

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Basic Ejector

SBP HV 2 04 7 KU

Part no...:10.02.01.01958

<https://www.schmalz.com/10.02.01.01958>



SEP HV 2 04 7

Part no...:10.02.01.01393

Shape: High Vacuum

Number of stages: 2

Nozzle size: 0.4 mm

Hole diameter: 7 mm

Degree of evacuation: 79 %

Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 13.2 l/min

Air consumption suction: 6.5 l/min



SHC 2 7

Part no...:10.02.01.01510

Number of stages: 2

Hole diameter: 7 mm

External diameter D: 6 mm

Length L: 6 mm

Thread G1: M8x0.5-M

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de