

## Vacuum filter (inline)

VFI 4/2 50

Part no...:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Vacuum Filters > Inline Filters VFI > VFI 4/2 50


### Vacuum filter with replaceable filter cartridge



Connection: Hose 4/2

Filter pore size: 50 µm

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 4 mm  |
| D         | 17 mm |
| L         | 55 mm |

### Technical Data

| Attribute                  | Value     |
|----------------------------|-----------|
| Connection                 | Hose 4/2  |
| Filter pore size           | 50 µm     |
| Nominal flow rate          | 32 l/min  |
| Nominal flow rate          | 1.92 m³/h |
| Max. vacuum                | -990 mbar |
| Overpressure (max) at 25°C | 7 bar     |
| Overpressure (max) at 50°C | 5 bar     |
| Weight                     | 6.30 g    |
| Product family             | VFI       |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Vacuum filter (inline)

VFI 4/2 50

Part no.:10.07.01.00329

<https://www.schmalz.com/10.07.01.00329>

### Accessories



#### FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)

### Spare parts



#### FILT-EINS 50 10x21 VFI

Part no.:10.07.01.00244

Filter pore size: 50 µm

External diameter D: 10.4 mm

Length L: 20.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)