

Sealing profile (meter)

DI-PROF 8x14 MOS NK-20 DL

Part no.:10.07.04.00012

<https://www.schmalz.com/10.07.04.00012>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 8x14 MOS NK-20 DL

Sealing section for construction of specific gripper solutions



Width B: 8 mm

Height H: 14 mm


Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Form: with sealing lip

Design Data



Attribute	Value
B	8 mm
H	14 mm
H1	7 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Natural Rubber NK
Recommended slot width x slot depth [mm]	9 x 6.5
Weight	54 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Sealing profile (meter)

DI-PROF 8x14 MOS NK-20 DL

Part no.:10.07.04.00012

<https://www.schmalz.com/10.07.04.00012>

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 |
customercenter@schmalz.de