

Vacuum hose (meter)

VSL 71-60 PU-DS-AS TR

Part no.:10.07.09.00065

<https://www.schmalz.com/10.07.09.00065>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 71-60 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 71 mm

Internal diameter d: 60 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 156 mm

Pressure range (operating pressure): -1.00 ... 2.92 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	60 mm
D	71 mm

Technical Data

Attribute	Value
Hose type	71-60
Pressure range (operating pressure)	-1.00 ... 2.92 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	156 mm
Length max.	15 m
Weight/Meter	1180 g/m
Weight/Meter	1.18 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 71-60 PU-DS-AS TR

Part no.:10.07.09.00065

<https://www.schmalz.com/10.07.09.00065>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 65-70 ST-VZ

Part no.:10.07.10.00098

Clamping range: 65.0 ... 70.0 mm

Material: Steel

Surface: galvanised