

Plug union, elbow

STV-W G3/8-AG 8

Part no.:10.08.02.00236

<https://www.schmalz.com/10.08.02.00236>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G3/8-AG 8

Push-in Fitting, swivelling elbow



Thread G1: G3/8"-M


Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 23.7 mm

Design Data



Attribute	Value
d	8 mm
G1	G3/8"-M
dn	6.50 mm
D1	14.30 mm
H	16 mm
H1	23.90 mm
L	23.70 mm
L1	34.60 mm
LG1	7.50 mm
SW1	20 mm
SW3	16 mm

Technical Data

Attribute	Value
Hose type	Hose D = 8 d = 6
Hose type	8-6
Material	Nickel plated
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	48 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Plug union, elbow

STV-W G3/8-AG 8


Part no.:10.08.02.00236

<https://www.schmalz.com/10.08.02.00236>

Product family

STV

Accessories



VSL 8-6 PE BL

Part no.:10.07.09.00015

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 8-6 PU MI-TR

Part no.:10.07.09.00003

External diameter D: 8 mm

Internal diameter d: 6 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 45 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -35 ... 60 °C

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de