

Multi-Base

VC-M-B 170x165x209

Part no...:10.01.12.01854

<https://www.schmalz.com/10.01.12.01854>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Manual Work > Multi-Clamp System VC-M / VC-M-V > VC-M-B 170x165x209

Turning and slewing device Base




Length L: 170 mm

Width B: 165 mm

Height H: 209 mm

Design Data



Attribute	Value
B	165 mm
H	209 mm
L	170 mm

Technical Data

Attribute	Value
Weight	4.70 kg

Accessories

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Multi-Base

VC-M-B 170x165x209

Part no...:10.01.12.01854

<https://www.schmalz.com/10.01.12.01854>



VC-M-SP 160x160x30

Part no...:10.01.12.01836

Length L: 160 mm

Width B: 160 mm

Height H: 30 mm

Air consumption: 48 l/min

Air consumption: 2.88 m³/h

Suction rate: 2.3 m³/h

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de