

## Vacuum filter (inline)

VFI CN8/6 50

Part no.:10.07.01.00245

<https://www.schmalz.com/10.07.01.00245>

Home > Vacuum Lifters and Crane Systems > Vacuum Lifting Device VacuMaster > Spare and Wear Parts Vacuum Lifting Devices VacuMaster > Spare Parts VacuMaster Basic / Comfort > VFI CN8/6 50


### Vacuum filter with replaceable filter cartridge



Connection: Hose 8/6 with Cap nut

Filter pore size: 50 µm

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 8 mm  |
| D         | 23 mm |
| L         | 68 mm |

### Technical Data

| Attribute                  | Value                 |
|----------------------------|-----------------------|
| Connection                 | Hose 8/6 with Cap nut |
| Filter pore size           | 50 µm                 |
| Nominal flow rate          | 66 l/min              |
| Nominal flow rate          | 3.96 m³/h             |
| Max. vacuum                | -990 mbar             |
| Overpressure (max) at 25°C | 7 bar                 |
| Overpressure (max) at 50°C | 5 bar                 |
| Weight                     | 10 g                  |

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Vacuum filter (inline)

VFI CN8/6 50


Part no.:10.07.01.00245

<https://www.schmalz.com/10.07.01.00245>

Product family

VFI

### Spare parts



#### FILT-EINS 50 16x23 VFI

Part no.:10.07.01.00248


Filter pore size: 50 µm

External diameter D: 16.2 mm

Length L: 22.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)



#### FILT-EINS 50 16x23 VFI

Part no.:10.07.01.00248

Filter pore size: 50 µm

External diameter D: 16.2 mm

Length L: 22.5 mm

Packaging unit: 5 pieces

Construction use: Vacuum filter (inline)

### Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)