

Vacuum hose (meter)

VSL 48-38 PVC-DS KL-TR

Part no.:10.07.09.00009

<https://www.schmalz.com/10.07.09.00009>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 48-38 PVC-DS KL-TR

Hose for vacuum and compressed-air systems



External diameter D: 48 mm

Internal diameter d: 38 mm

Length max.: 50 m


Material hose: PVC with wire spiral

Bending radius min.: 120 mm

Pressure range (operating pressure): -0.88 ... 7.00 bar

Operating temperature: -15 ... 65 °C

Design Data



Attribute	Value
d	38 mm
D	48 mm

Technical Data

Attribute	Value
Hose type	48-38
Pressure range (operating pressure)	-0.88 ... 7.00 bar
Operating temperature	-15 ... 65 °C
Bending radius min.	120 mm
Length max.	50 m
Weight/Meter	896 g/m
Weight/Meter	0.90 kg/m
Material hose	PVC with wire spiral

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 48-38 PVC-DS KL-TR

Part no...:10.07.09.00009

<https://www.schmalz.com/10.07.09.00009>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSB 32-50 ST-VZ

Part no...:10.07.10.00004

Clamping range: 32.0 ... 50.0 mm

Material: Steel

Surface: galvanised



SSB 40-60 ST-VZ

Part no...:10.07.10.00005

Clamping range: 40.0 ... 60.0 mm

Material: Steel

Surface: galvanised



ST G1-1/2-AG 38 MS-V

Part no...:10.08.03.00170

Thread G1: G1-1/2"-M

Hose diameter (rec.) d: 38 mm

Material: Brass

Surface: nickel plated

Length L: 12.2 mm

Nominal diameter dn: 29.9 mm

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 48-38 PVC-DS KL-TR

Part no.:10.07.09.00009

<https://www.schmalz.com/10.07.09.00009>
