

Vacuum hose (meter)

VSL 86-75 PU-DS-AS TR

Part no.:10.07.09.00054

<https://www.schmalz.com/10.07.09.00054>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 86-75 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 86 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 66 mm

Pressure range (operating pressure): -0.50 ... 1.69 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	75 mm
D	86 mm

Technical Data

Attribute	Value
Hose type	86-75
Pressure range (operating pressure)	-0.50 ... 1.69 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	66 mm
Length max.	15 m
Weight/Meter	1050 g/m
Weight/Meter	1.05 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Vacuum hose (meter)

VSL 86-75 PU-DS-AS TR

Part no.:10.07.09.00054

<https://www.schmalz.com/10.07.09.00054>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 80-85 ST-VZ

Part no.:10.07.10.00136

Clamping range: 80.0 ... 85.0 mm

Material: Steel

Surface: galvanised