

Mounting profile

MO-PROF 40 3TN AL-1

Part no.: 26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Sections and Connectors > Mounting Profiles MO-PROF > MO-PROF 40 3TN AL-1

Aluminium profile for construction of vacuum-gripping systems




Width B: 40 mm

Length max.: 6,000 mm

Form: with 3 T-slots

Material: Al Mg Si 0.5 F22

Design Data



Attribute	Value
B	40 mm
B1	20 mm
B3	5.20 mm
d	4.60 mm
H1	20.50 mm
H2	10 mm
Length (max.)	6000 mm

Note: Additional costs for cut

Technical Data

Attribute	Value
Area	6.50 cm ²
Resistance moment W _x	5.50 cm ³
Resistance moment W _y	5.20 cm ³
Area moment I _x	12.70 cm ⁴
Area moment I _y	10.40 cm ⁴
Warping max.	0.80 mm/m
Material	Al Mg Si 0.5 F22

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mounting profile

MO-PROF 40 3TN AL-1


Part no.:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>

Mass	1.80 kg/m
Product family	MO-PROF

Note: There are additional costs for cutting!


Accessories



BEF-WIN 40x40x40 5 MO-PROF

Part no.:25.09.06.00007

Width B: 40 mm
Height H: 40 mm
Length L: 40 mm
Wall thickness s: 5 mm
Construction use: Mounting section
Weight: 107 g



DI-RA 40 PPTA MO-PROF

Part no.:10.07.08.00131

Height H: 1 mm
Length L: 40 mm
Wall thickness s: 10.5 mm
Construction use: Mounting section
Weight: 2 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mounting profile

MO-PROF 40 3TN AL-1

Part no.:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



NUT-STEI 10x20 M6-IG

Part no.:25.09.06.00002

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 10 mm

Thread G1: M6-F

Shape mounting elements: With step

Surface: galvanised

Weight: 6 g



NUT-STEI 10x20 M8-IG

Part no.:25.09.06.00003

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 10 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 5 g



NUT-STEI 20x20 M8-IG 10

Part no.:25.09.06.00012

Width B: 20 mm

Height H: 4.9 mm

Material: Steel

Length L: 20 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 15.9 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mounting profile

MO-PROF 40 3TN AL-1

Part no.: 26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



SCHR WN1552 5x20 ST VZ T25

Part no.: 20.10.03.00008

External diameter D: 5 mm

Material: Steel

Length L: 20 mm

Surface: galvanised

Weight: 3.9 g



VBR-PR 150x3 E-FL


Part no.: 25.09.06.00006

Height H: 3 mm

Length L: 150 mm

Weight: 362 g

Connection 1: 2 Sliding blocks



VBR-PR 185x185x3 K-FL

Part no.: 25.09.06.00005

Width B: 185 mm

Height H: 3 mm

Length L: 185 mm

Weight: 279 g

Connection 1: 2 sliding blocks

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mounting profile

MO-PROF 40 3TN AL-1

Part no...:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



VBR-PR 40x55x55 E-V

Part no...:10.08.03.00099

Width B: 55 mm

Height H: 55 mm

Length L: 40 mm

Wall thickness s: 6 mm

Weight: 164 g



VRS-PL-40 G1/2-IG MO-PROF

Part no...:25.09.06.00009

Height H: 10 mm

Length L: 40 mm

Thread G1: G1/2"-F

Construction use: Mounting section

Weight: 72 g



VRS-PL-40 MO-PROF

Part no...:25.09.06.00026

Height H: 5 mm

Material: Polyamide

Length L: 40 mm

Construction use: Mounting section

Weight: 11.1 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Mounting profile

MO-PROF 40 3TN AL-1

Part no.:26.07.01.00022

<https://www.schmalz.com/26.07.01.00022>



VRS-PL-40 MO-PROF

Part no.:25.09.06.00008

Height H: 4 mm

Material: Steel

Length L: 40 mm

Construction use: Mounting section

Weight: 45 g

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de