

Flat suction cup (oval)

SGON 7x3.5 NBR-55 M3-AG

Part no.:10.01.01.00489

<https://www.schmalz.com/10.01.01.00489>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 7x3.5 NBR-55 M3-AG

Flat suction cup (oval) for long and also curved workpieces



Dimensions (LxB): 7 x 3.5


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: M3-M

Design Data



Attribute	Value
Bmax(S)	4.50 mm
Bs	3.50 mm
dn	1 mm
G1	M3-M
H	8 mm
LG1	3 mm
Lmax(S)	7.50 mm
Ls	7 mm
SW1	5 mm
Z (Stroke)	0.80 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technical Data

Attribute	Value
Suction force (-600mbar)	1 N
Volume	0.03 cm ³
Curve radius (min) (convex)	3 mm
Hose diameter (rec.) d	2 mm
Dimensions (LxB)	7 x 3.5
Number of folds	0
Suction cup material	Nitrile rubber NBR

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (oval)

SGON 7x3.5 NBR-55 M3-AG

Part no.:10.01.01.00489

<https://www.schmalz.com/10.01.01.00489>

Material hardness [Shore A]	55 Shore A
Weight	2 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N003 M3-AG DN100

Part no.:10.01.01.00316

Thread G1: M3-M
Length L1: 7.5 mm
Fitting length: 2 mm
Material: Aluminum



SGO 7x3.5 NBR-55 N003

Part no.:10.01.01.00488

Dimensions (LxB): 7 x 3.5
Suction cup material: Nitrile rubber NBR
Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de