

## Vacuümpomp

EVE-OG 40 AC3

Onderdeelnr.:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>

Homepage > Vacuümtechniek voor de automatisering > Vacuüm componenten > Vacuümgenerator > Vacuümpompen > Oil-Lubricated Vacuum Pumps EVE-OG > EVE-OG 40 AC3

### Oliegesmeerde vacuümpomp met maximaal vacuümniveau, onderhoudsarm



Current type: three-phase current

Sound level at 50 Hz: 64 dB(A)


Suction rate (50 Hz): 40 m<sup>3</sup>/h

Rated power 50 Hz: 1,1 kW

Voltage at 50Hz: 230/400±10%

Weight: 38 kg

### Ontwerpgegevens



| Attribuut | Waarde     |
|-----------|------------|
| B         | 284 mm     |
| B2        | 15 mm      |
| G3        | G1-1/4"-IG |
| G5        | M8-IG      |
| H         | 260 mm     |
| L         | 625 mm     |
| L2        | 130 mm     |
| X1        | 179 mm     |
| X2        | 123 mm     |
| Y1        | 238 mm     |
| Y2        | 171 mm     |

### Technische gegevens

| Attribuut            | Waarde               |
|----------------------|----------------------|
| Max. vacuum          | -980 mbar            |
| Max. vacuum          | -28,94 inHg          |
| Suction rate (50 Hz) | 40 m <sup>3</sup> /h |
| Voltage at 50Hz      | 230/400±10%          |
| Rated power 50 Hz    | 1,10 kW              |
| Sound level at 50 Hz | 64 dB(A)             |

### Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Vacuümpomp

EVE-OG 40 AC3

Onderdeelnr...:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>

|                    |        |
|--------------------|--------|
| Weight             | 38 kg  |
| Protection type IP | IP 54  |
| Current type       | AC3    |
| Product family     | EVE-OG |

### Accessoires



#### DRM 40 P1 H

Onderdeelnr...:10.07.02.00050

External diameter D: 40 mm

Measuring range: 0,0 ... 1,0 bar

Construction shape manometers: Aansluiting achter

Thread G1: G3/4"-M



#### MSS-K 2.5-4A

Onderdeelnr...:10.04.04.00120

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

### Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Vacuümpomp

EVE-OG 40 AC3

Onderdeelnr...:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>



### VOL 50

Onderdeelnr...:10.03.03.00118

Reservoirs volume: 50 l

Height H: 235 mm

Add. function: Manometer, valve, filter



### ZUB EVE-OG Ölablass-Kit

Onderdeelnr...:22.09.03.00038

Construction use: Pump EVE-OG

## Onderdelen



### FILT-EINS 3 98x70 PAP STF-1-1/4-IGN

Onderdeelnr...:10.07.01.00018

Filter pore size: 3 µm

External diameter D: 98 mm

Length L: 70 mm

Filter material: Papier

Construction use: Dust filter STF

Size: 1-1/4-IGN

### Contact opnemen met Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Vacuümpomp

EVE-OG 40 AC3

OnderdeelNr...:10.03.02.00026

<https://www.schmalz.com/10.03.02.00026>



### OEL EVE-OG 1L ANDEROL 555

OnderdeelNr...:27.02.01.00055

Construction use: Pump EVE-OG



### VST EVE-OG-25-40

OnderdeelNr...:10.03.02.00060

Construction use: Pump EVE-OG

Size: 25-40