

Flat suction cup (round)

PFYN 1.5 NBR-CO-55 M3-AG

Part no.:10.01.01.10376

<https://www.schmalz.com/10.01.01.10376>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 1.5 NBR-CO-55 M3-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 1.5


Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: M3-M

Design Data



Attribute	Value
dn	0.70 mm
Dmax(S)	1.80 mm
Ds	1.50 mm
G1	M3-M
H	4.50 mm
LG1	3 mm
SW1	5 mm
Z (Stroke)	0.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0.06 N
Volume	0.00 cm ³
Curve radius (min) (convex)	2 mm
Hose diameter (rec.) d	2 mm
Size	1.50
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

PFYN 1.5 NBR-CO-55 M3-AG

Part no.:10.01.01.10376

<https://www.schmalz.com/10.01.01.10376>

Weight 1 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N002 M3-AG DN70


Part no.:10.01.01.00314

Thread G1: M3-M

Length L1: 6.5 mm

Fitting length: 2 mm

Material: Aluminum



PFG 1.5 NBR-CO-55 N002

Part no.:10.01.01.10336

Size: 1.5

Suction cup material: Nitrile rubber NBR-conductive

Material hardness [Shore A]: 55 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de