

Bellows suction cups (round)

FSGA 2 HT1-60 M3-AG

Part no.:10.01.06.04523

<https://www.schmalz.com/10.01.06.04523>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSGA (1.5 Folds) > FSGA 2 HT1-60 M3-AG

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 2

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A


Nipple material: Aluminum

Connection: M3-M

Number of folds: 1.5

Vacuum connection: M3-M

Design Data



Attribute	Value
d2	1.30 mm
Dmax(S)	4 mm
dn	1 mm
Ds	1.90 mm
G1	M3-M
H	6.50 mm
LG1	3 mm
SW1	5 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60 Shore A
Size	2
Number of folds	1.50
Connection	M3-AG
Curve radius (min) (convex)	1 mm
Volume	0.02 cm ³

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Bellows suction cups (round)

FSGA 2 HT1-60 M3-AG

Part no.:10.01.06.04523

<https://www.schmalz.com/10.01.06.04523>

Suction force (-600mbar)	0.08 N
Pull-off force	0.15 N
Hose diameter (rec.) d	3 mm
Weight	0.20 g
Product family	FSGA

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



FGA 2 HT1-60 N003

Part no.:10.01.06.04519

Size: 2

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 1.5



SA-NIP N003 M3-AG DN100

Part no.:10.01.01.00316

Thread G1: M3-M

Length L1: 7.5 mm

Fitting length: 2 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de