

Flat suction cup (oval)

SAOF 100x50 NBR-60 RA

Osanro.:10.01.05.00302

<https://www.schmalz.com/10.01.05.00302>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Imukahva metallilevyn käsittelyyn > Flat Suction Cups SAOF (Oval) > SAOF 100x50 NBR-60 RA

Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 100x50


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: RA

Suunnitteludata



Attribuutti	Arvo
Bmax(S)	54 mm
Bs	48,10 mm
dn	6 mm
H	25 mm
L4	32 mm
Lmax(S)	106 mm
Ls	101,10 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	217 N
Lateral force	181 N
Lateral force (oily surface)	121 N
Volume	21,80 cm ³
Curve radius (min) (convex)	75 mm
Hose diameter (rec.) d	6 mm
Number of folds	0

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Sivu 1 alkaen 2

Flat suction cup (oval)

SAOF 100x50 NBR-60 RA

Osanro.:10.01.05.00302

<https://www.schmalz.com/10.01.05.00302>

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Weight	72 g
Product family	SAOF
Dimensions (LxB)	100x50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m