

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Osanro.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>

Aloitussivu > Alipainetekniikkaa automaatioon > Alipainekomponentit > Imukupit > Litteä imukuppi (soikea) > Flat Suction Cups SGON > SGON 30x10 SI-HD-65 G1/8-IG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: G1/8"-F

Suunnitteludata



Attribuutti	Arvo
Bmax(S)	11,50 mm
Bs	9,40 mm
dn	2,50 mm
G1	G1/8"-F
H	25 mm
LG1	9 mm
Lmax(S)	30,50 mm
Ls	29,40 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Tekniset tiedot

Attribuutti	Arvo
Suction force (-600mbar)	12,20 N
Volume	0,52 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Ota yhteyttä Schmalziin

Oy Schmalz Ab | Taivaltie 5, 01610 Vantaa, Finland | +358 10 2312011 | schmalz@schmalz.fi

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Osanro.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>

Weight	7,50 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Varaosat



SGO 30x10 SI-HD-65 N022

Osanro.:10.01.05.01037

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N022 G1/8-IG DN350

Osanro.:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 13 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Flat suction cup (oval)

SGON 30x10 SI-HD-65 G1/8-IG

Osanro.:10.01.05.01053

<https://www.schmalz.com/10.01.05.01053>



ZOKL 11-13

Osanro.:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel