

Flat suction cup (round)

SGA 13 PU-55 N029

Part no.:10.01.01.00571

<https://www.schmalz.com/10.01.01.00571>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SGA 13 PU-55 N029

Flat suction cup (round)




Size: 13

Suction cup material: Polyurethane PU

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	8.80 mm
d1	11.90 mm
Dk	14.80 mm
Dmax(S)	13.50 mm
Ds	12 mm
H	11.50 mm
H2	1.80 mm
H3	3.60 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	13
Suction cup material	Polyurethane PU
Suction force (-600mbar)	4.70 N
Material hardness [Shore A]	55 Shore A
Volume	0.44 cm ³
Curve radius (min) (convex)	12.50 mm
Number of folds	0

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Flat suction cup (round)

SGA 13 PU-55 N029

Part no.:10.01.01.00571

<https://www.schmalz.com/10.01.01.00571>

Weight	1.30 g
Product family	SGA

Accessories



SA-NIP N029 G1/8-AG DN350

Part no.:10.01.01.00816

Thread G1: G1/8"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N029 G1/8-IG DN350

Part no.:10.01.01.00815

Thread G1: G1/8"-F

Fitting length: 13 mm

Material: Aluminum

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de