

Suction plate (round)

SPU 100 SI-60 G1/4-IG

Part no.:10.01.01.01108

<https://www.schmalz.com/10.01.01.01108>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Suction Plates SPU > SPU 100 SI-60 G1/4-IG

Suction plate (round), universal, for smooth and slightly rough surfaces




Size: 100

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Connection: G1/4"-F

Design Data



Attribute	Value
d	22 mm
d2	60 mm
Dmax(S)	108 mm
Ds	100 mm
G1	G1/4"-F
H	25 mm
H1	26 mm
LG1	13 mm
Z (Stroke)	7 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	425 N
Suction force d2	185 N
Volume	44.30 cm ³
Curve radius (min) (convex)	130 mm
Hose diameter (rec.) d	9 mm
Size	100
Suction cup material	Silicone SI

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de

Suction plate (round)

SPU 100 SI-60 G1/4-IG

Part no...:10.01.01.01108

<https://www.schmalz.com/10.01.01.01108>

Material hardness [Shore A]	60 Shore A
Weight	100 g
Number of folds	0
Product family	SPU

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SU 100

Part no...:10.01.01.12840

Size: 100

Clamping range: 100.0 ... 115.0 mm

Temperature resistance: 80 °C

Spare parts



DR-SPU 100 SI-60

Part no...:10.01.01.01105

Size: 100

Suction cup material: Silicone SI

Material hardness [Shore A]: 60 Shore A

Contact Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Str.1, 72293 Glatten, Germany | +49 7443 2403-102 | customercenter@schmalz.de